

Product Name : LED Lamp
 Country of origin : China
 Introduction :
 This product can protect your eyes and place anywhere easily, especially when you use smart phone, panel or computer in dark environment.

Operating Instructions

- 1.LED Lighting area
- 2.LOGO (Backlight)
- 3.Adjustable Stand
- 4.Touch Power Switch
- 5.Color Temperature Switch
- 6.Touch Dimmer
- 7.Indicator of charge and low battery notification
- 8.Charge input




EYE PROTECTION SURFACE LED LAMP

Users Manual

1. Turn On/Turn Off ④
Touch the Power switch
2. Colour Temperature ⑤
Touch it to switch 3 modes.
Warm White 3100K (Use smart phone in dark place)
Neutral White 4200K (Reading use)
Cool White 5400K (Writing use)
3. Dimming Control ⑥
From left to right by finger slide to increase light
From right to left by finger slide to decrease light
4. Low Battery Notification ⑦
Blue LED on the front indicates it only have 10~20 mins to use and needs to charge.
5. To Charge(2~3 hrs) ⑦+⑧
Red LED on the bottom indicates it is charging. Light will go off once it is fully charged.

Using Time : 3~30 hrs (depend on brightness)
 Please use the original cable when charging.

Using in Correct method



Wrong using method



Specification

Battery Type : Li-Polymer
 Battery Capacity : 2000mAh
 Dimension : 56.2*6.5*2.1cm
 Unit Of Weight : 385g
 Working Temp. : -20°C~50°C
 Power Consumption: 6.25W (When charging and using neutral white light)
 Input : DC 5V1A
 Color Temperature :
 Warm White 3100K
 Cool White 5400K
 Neutral White 4200K
 Luminous Flux :
 Warm White 49.30~108.4 lm/w
 Cool White 54.35~108.1 lm/w
 Neutral White 50.47~102.7 lm/w
 LED Lamp Wattage :
 Warm White 0.09~2.43 W
 Cool White 0.13~2.41 W
 Neutral White 0.19~3.75 W
 Wavelength Range :
 Warm White 581.2~581.4 nm
 Cool White 551.2~554.0 nm
 Neutral White 579.3~579.7 nm